



Representative Image

Catalog No. DF2417FRAB0

Description: 200A,REC,3P4W,MG,417,39208V,FC

UPC No 708917311195

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Receptacle with Angle Adapter and Junction Box, 200 Amp, 3 Pole 4 Wire, 30 208V, 400Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Electrical hook-up of mobile medical imaging (MMI) trailers.

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	200 Amps
Voltage Rating	208 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Construction type	Wall socket
Number of poles	3