



Representative Image

## Catalog No. DF2421FR000

**Description:** 200A,REC,3P4W,MG,421,3P440

**UPC No** 708917157779

**Home > Connectivity & Grounding > Russellstoll > Electrical receptacles**

MaxGard Female Flap Cap Receptacle, 200 Amp, 3 Pole 4 Wire, 30 440V, 60Hz

### Descriptors

|                  |                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical receptacles                                                                                                                                           |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | Electrical hook-up of mobile medical imaging (MMI) trailers.                                                                                                     |

### Specifications

|          |               |
|----------|---------------|
| Material | Cast Aluminum |
|----------|---------------|

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

|                   |                                              |
|-------------------|----------------------------------------------|
| ETIM              | EC001322 Round socket/plug for high currents |
| Amperage          | 200 A                                        |
| Construction type | Wall socket                                  |
| Number of poles   | 3                                            |