



Representative Image

Catalog No. DF2523FRAB0

Description: 300A,REC,4P5W,MG,523,3PY480V

UPC No 708917303947

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Receptacle with Angle Adapter and Junction Box, 200 Amp, 4 Pole 5 Wire, Reserved,

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Electrical hook-up of mobile medical imaging (MMI) trailers.

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	300 Amps
Voltage Rating	480 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM	EC001322 Round socket/plug for high currents
Amperage	300 A
Construction type	Wall socket
Number of poles	4