



Representative Image

Catalog No. DF3104FR000

Description: 30A,REC,2P3W,MG,104,277

UPC No 708917175339

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

Maxgard Female Receptacle, 30Amp, 2 Pole 3 Wire, 277V, 60Hz

Descriptors

Category	Electrical receptacles
----------	------------------------

Specifications

Number Of Poles	2
Number Of Wires	3
Amperage Rating	30 Amps
Voltage Rating	277 V

Classifications

Brand Name	Russellstoll
Sub Brand	MaxGard

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Wall socket
Number of poles	2