



Representative Image

Catalog No. DF3107FRA00

Description: 30A,REC,2P3W,MG,125V,AGL,FC

UPC No 708917312185

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

MaxGard Female Receptacle with Angle Adapter, 30 Amp, 2 Pole 3 Wire, 125V, 60Hz

Descriptors

| | |
|------------------|---|
| Category | Electrical receptacles |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application | For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport. |

Specifications

| | |
|----------|---------------|
| Material | Cast Aluminum |
|----------|---------------|

Classifications

| | |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

| | |
|-------------------|--|
| ETIM | EC001322 Round socket/plug for high currents |
| Amperage | 30 A |
| Construction type | Wall socket |
| Number of poles | 2 |

by ABB