



Representative Image

Catalog No. DF3307FP000

Description: 30A,CON,3P4W,MG,307,125/250

UPC No 708917193128

Home > Connectivity & Grounding > Russellstoll > Electrical receptacles

MaxGard Female Flap Cap Connector, 30 Amp, 3 Pole 4 Wire, 125/250V, 60Hz

Descriptors

Category	Electrical receptacles
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport.

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Number of poles	3