



Representative Image

Catalog No. DS1404FRABK

Description: 100A,REC,3P4W,MG,404,ABK,3P480V

UPC No 708917182665

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Screw Cap Female Receptacle with Angle Adapter, Junction Box and Control Contacts, 3 Pole 4 Wire, 100 Amp, 30 480V-60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Convention centers and areanas

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	100 Amps
Voltage Rating	480 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	100 A
Number of poles	3