



Representative Image

Catalog No. DS1414MP00K

Description: 100A,PLG,3P4W,MG,414,00K,3P600V

UPC No 708917270546

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Screw Cap Male Plug with Control Contacts, 100 Amp, 3 Pole 4 Wire, 30 600V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Convention centers and areanas

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	100 Amps
Voltage Rating	600 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
Standard	UL e68085 UL e68085

ETIM	EC001322 Round socket/plug for high currents
Amperage	100 A
Construction type	Plug
Number of poles	3