



Representative Image

## Catalog No. DS1504MP00K

**Description: 100A,PLG,4P5W,MG,504,00K,3PY277V**

**UPC No 708917181781**

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Male Plug with Control Contacts, 100 Amp, 4 Pole 5 Wire, 30Y 277/480V, 60Hz

### Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Convention centers and arenas

### Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	100 Amps
Voltage Rating	277 V
Material	Cast Aluminum

### Classifications

Brand Name	Russellstoll
Standard	UL e68085 UL e68085

ETIM	EC001322 Round socket/plug for high currents
Amperage	100 A
Construction type	Plug
Number of poles	4

