



Representative Image

## Catalog No. DS2404FRAB0

**Description:** 200A,REC,3P4W,MG,404,AB0,3P480V

**UPC No** 708917150183

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Female Receptacle with Angle Adapter, Junction Box, and Screw Cap, 200 Amp, 3 Pole 4 Wire, 30 480V, 60Hz

### Descriptors

|                  |                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical sleeves                                                                                                                                               |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | Electrical hook-up of mobile medical imaging (MMI trailers).                                                                                                     |

### Specifications

|                 |               |
|-----------------|---------------|
| Number Of Poles | 3             |
| Number Of Wires | 4             |
| Amperage Rating | 200 Amps      |
| Voltage Rating  | 480 V         |
| Material        | Cast Aluminum |

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

### ETIM Classification

|                 |                                              |
|-----------------|----------------------------------------------|
| ETIM            | EC001322 Round socket/plug for high currents |
| Amperage        | 200 A                                        |
| Number of poles | 3                                            |