



Representative Image

## Catalog No. DS2407MP00K

**Description:** 200A,PLG,3P4W,MG,407,00K,3P250V

**UPC No** 708917198512

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Male Plug with Control Contacts, 200 Amp, 3 Pole 4 Wire, 30 250V, 60Hz

### Descriptors

|                  |                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical sleeves                                                                                                                                               |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight"). |
| Application      | Electrical hook-up of mobile medical imaging (MMI trailers).                                                                                                     |

### Specifications

|                 |               |
|-----------------|---------------|
| Number Of Poles | 3             |
| Number Of Wires | 4             |
| Amperage Rating | 200 Amps      |
| Voltage Rating  | 250 V         |
| Material        | Cast Aluminum |

### Classifications

|            |              |
|------------|--------------|
| Brand Name | Russellstoll |
|------------|--------------|

|                   |                                              |
|-------------------|----------------------------------------------|
| ETIM              | EC001322 Round socket/plug for high currents |
| Amperage          | 200 A                                        |
| Construction type | Plug                                         |
| Number of poles   | 3                                            |