



Representative Image

Catalog No. DS2514FRAB0

Description: 200A,REC,4P5W,MG,514,AB0,3PY347V

UPC No 708917154372

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Receptacle with Angle Adapter and Junction Box, 200 Amp, 4 Pole 5 Wire, 30Y 347/600V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Electrical hook-up of mobile medical imaging (MMI trailers).

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	200 Amps
Voltage Rating	347 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
------------	--------------

ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	200 A
Number of poles	4