



Representative Image

Catalog No. DS3104MP000

Description: 30A,PLG,2P3W,MG,104,277V

UPC No 708917201571

Home > Connectivity & Grounding > Russellstoll > Electrical plugs

Maxgard Male Plug, 30Amp, 2 Pole 3 Wire, 277V, 60Hz

Descriptors

Category	Electrical plugs
----------	------------------

Specifications

Number Of Poles	2
Number Of Wires	3
Amperage Rating	30 Amps
Voltage Rating	277 V

Classifications

Brand Name	Russellstoll
Standard	UL e68085 UL e68085

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Plug
Number of poles	2