



Representative Image

## Catalog No. DS3407MP00K

**Description:** 30A,PLG,3P4W,MG,407,00K,3P250V

**UPC No** 708917300243

**Home > Connectivity & Grounding > Russellstoll > Electrical sleeves**

MaxGard Male Plug with Control Contacts, 30 Amp, 3 Pole 4 Wire, 30 250V, 60Hz

### Descriptors

|                  |                                                                                                                                                                         |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Category         | Electrical sleeves                                                                                                                                                      |
| Special Features | Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").        |
| Application      | For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport. |

### Specifications

|                 |               |
|-----------------|---------------|
| Number Of Poles | 3             |
| Number Of Wires | 4             |
| Amperage Rating | 30 Amps       |
| Voltage Rating  | 250 V         |
| Material        | Cast Aluminum |

### Classifications

|            |                        |
|------------|------------------------|
| Brand Name | Russellstoll           |
| Standard   | UL e68085<br>UL e68085 |

|                   |                                              |
|-------------------|----------------------------------------------|
| ETIM              | EC001322 Round socket/plug for high currents |
| Amperage          | 30 A                                         |
| Construction type | Plug                                         |
| Number of poles   | 3                                            |