



Representative Image

Catalog No. DS3504FP000

Description: 30A,PLG,3P4W,MG,404,000,3P480V,FC

UPC No 708917300915

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Female Connector, 30 Amp, 3 Pole 4 Wire, 30Y 277/480V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport.

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	30 Amps
Voltage Rating	480 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Plug
Number of poles	3

by ABB