



Catalog No. DS3511MP000

Description: 30A,PLG,4P5W,MG,511,220/115V

UPC No 708917298601

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Motor Inlet, Voltage 3 Phase Y 220/380V, Amperage 30A, 4 Poles 5 Wire, with Screw Cap

Descriptors

Category	Electrical sleeves
----------	--------------------

Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	30 Amps
Voltage Rating	220/380 V

Classifications

Brand Name	Russellstoll
Standard	UL e68085 UL e68085

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Plug
Number of poles	4