



Representative Image

Catalog No. DS3521MP000

Description: 30A,PLG,4P5W,MG,521,3PY250V

UPC No 708917176244

Home > Connectivity & Grounding > Russellstoll > Electrical plugs

MaxGard Male Plug, 30 Amp, 4 Pole 5 Wire, 30Y 250/440V, 60Hz

Descriptors	
Category	Electrical plugs
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use in "People Movers" which require aire conditioning and heater unit power when docked at end of line locations for maintenance and overhaul, ex: Dulles Airport.

Specifications	
Material	Cast Aluminum

Classifications	
Brand Name	Russellstoll
Standard	UL e68085 UL e68085

ETIM	EC001322 Round socket/plug for high currents
Amperage	30 A
Construction type	Plug
Number of poles	4