



Representative Image

Catalog No. DS4504FRABK

Description: 400A,REC,4P5W,MG,504,ABK,3PY277V

UPC No 708917239819

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

Female Receptacle with Angle Adapter and Junction Box, Voltage 3 Phase Y 277/480V, Amperage 400A, 4 Poles 5 Wire, with Screw Cap and 2 Control Contacts

Descriptors	
Category	Electrical sleeves
Specifications	
Number Of Poles	4
Number Of Wires	5
Amperage Rating	400 Amps
Voltage Rating	277/480 V
Classifications	
Brand Name	Russellstoll
ETIM Classification	
ETIM	EC001322 Round socket/plug for high currents
Amperage	400 A
Number of poles	4