



Representative Image

Catalog No. DS6404MP00K

Description: 60A,PLG,3P4W,MG,404,3P480V,CNTRLCNT

UPC No 708917178736

Home > Connectivity & Grounding > Russellstoll > Electrical sleeves

MaxGard Male Plug with Control Contacts, 60 Amp, 3 Pole 4 Wire, 30 480V, 60Hz

Descriptors

Category	Electrical sleeves
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	Power for trade show exhibits and concerts

Specifications

Number Of Poles	3
Number Of Wires	4
Amperage Rating	60 Amps
Voltage Rating	480 V
Material	Cast Aluminum

Classifications

Brand Name	Russellstoll
Standard	UL e68085 UL e68085

ETIM	EC001322 Round socket/plug for high currents
Amperage	60 A
Construction type	Plug
Number of poles	3