



## Catalog No. DBRS450440000/E400

Description: 400A ILK MG 504 4P5W 3PY480 4IN @ E

UPC No 708917346814

[Home](#) > [Connectivity & Grounding](#) > [Russellstoll](#) > [Electrical receptacles](#)

MaxGard Interlocked Receptacle with Circuit Breaker with Screw Cap, 400 Amp, 4 Pole 5 Wire, 3 Phase Y 277/480V, 60Hz, Breaker Trip Rating 400 Amp, 4 Inches at E

### Descriptors

Category	Electrical receptacles
Special Features	Waterproof construction provides environmental separation at the front of each device (they don't have to be connected together just to be called "watertight").
Application	For use with watertight plugs and inlets where portable equipment is on stand by and plugs are not in use.

### Specifications

Number Of Poles	4
Number Of Wires	5
Amperage Rating	400 Amps
Voltage Rating	277/480 V
Material	Cast Aluminum

### Classifications

Brand Name	Russellstoll
------------	--------------

### ETIM Classification

ETIM	EC001322 Round socket/plug for high currents
Amperage	400 A
Number of poles	4

by ABB