



Representative Image

## Catalog No. E71U

**Description: NONINS BS RNG TRM No6 1/4 BLT 90 DE**

**UPC No 786210861043**

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Non-Insulated Large Brazed Seam Ring Terminal with 90 Degree Bend, Length 1.13 Inches, Width .48 Inches, Bolt Hole 1/4 Inch, Wire Range #6 AWG, Copper, Tin Plated, 200 Pack

### Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indent or double indent (recommended for solid wire). Serrated barrel increases grip on wire.

### Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

### Classifications

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

### Dimensions

Wire Size	6 AWG
-----------	-------

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
Material	Copper

by ABB

ETIM	EC001052 Solderless copper terminals for copper conductors
Surface protection	Tinned
Stud size (imperial)	1/4 inch