



Catalog No. J972

Description: NON-INS TUB RING 1/0AN-2/0 5/16

UPC No 786210815664

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Tubular Ring Terminal, Length 1.94 Inches, Width .84 Inches, Bolt Hole 5/16 Inch, Wire Range 1/0AN-2/0, Copper, Tin Plated, 50 Pack

Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).

Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

Classifications

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

Dimensions

Wire Size	1/0AN-2/0
-----------	-----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N
With sight-hole	Y

by ABB

ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	1