



Representative Image

Catalog No. LH232AMV

Description: A32 DBL LOCK SYS 1XPG21-3/4 TOP

UPC No 786209988089

Home > Connectivity & Grounding > Pos-E-Kon > Terminal block covers

Reverse locking lever hoods (double), top entry, 32 contacts with ground connection, NPT entry - 1 Inch x 3/4 Inch

Descriptors

Category	Terminal block covers
----------	-----------------------

Specifications

Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Temperature Rating	-40 to +257 F

Classifications

Brand Name	Pos-E-Kon
Standard	UL E215386

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC000437 Housing for rectangular connectors
Width	56.007 mm
Height	75.9968 mm
Type of housing	Other
Material housing	Aluminium
Coating housing	Powder coating
Position cable feed	Sideways
With cable screw gland	N
With hinged lid	N
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125 °C
Degree of protection (IP), mounted	Other

by ABB