



Representative Image

Catalog No. LT50

Description: 1/2 BLACK STRAIGHT LIQUIDTIGHT FTG

UPC No 34481152019

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

1/2 Inch Black Liquidtight Non-metallic Omni Connector

Descriptors

Category	Liquid tight connectors
Special Features	No Disassembly Required.
Application	Suitable for Indoor/outdoor Use.

Specifications

Material	Non-metallic
Color	Black

Classifications

Brand Name	T&B Liquidtight Fittings
Sub Brand	Carlon
Standard	UL E23018

Dimensions

Size	1/2 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1/2 inch
Degree of protection (IP)	IP68
Model	Straight
Revolving thread	N
Construction type	External thread

by ABB

ETIM	EC001178 Screw connection for protective plastic hose
Type of connection	Plug-in connection
Thread connection size	Other
Thread length	15.9 mm
One-piece	Y
Total length	50.8 mm