



Representative Image

Catalog No. PAIR22-6

Description: PNEU TOOL TO CRIMP A-E, RA-RE C YOLK

UPC No 786210969008

Home > Connectivity & Grounding > Application Tooling > Wire lug crimping tool

Pneumatic Power Tool for Crimping A, B, C, D, E Non-insulated and RA, RB, RC, RD, RE Insulated Terminals/Splices/Disconnects, Open "c" Yolk, Wire Range #22 - 6 AWG

Descriptors

Category	Wire lug crimping tool
Special Features	Portable Hand-held Pneumatic, Open Yoke, Color-coded Dies
Application	Crimping Terminals/Splices/Disconnects

Specifications

Crimping Force	1.25 tons
----------------	-----------

Classifications

Brand Name	Application Tooling
------------	---------------------

Dimensions

Overall Length	14 in , 356 mm
----------------	----------------

Compliance and Certifications

RoHS	Out of scope of RoHS
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000168 Crimp tool cable lugs, cable end sleeves, screen connection
Suitable for	Various applications
AWG-range	22-6
Construction/operation	Pneumatic
Inserts exchangeable	Y

by ABB