



Representative Image

Catalog No. PM3212C

Description: LOAD CTR MCB 125A 32CKT N1 GRAY PON

UPC No 783164640519

Home > Load Centers > Load Centers

PowerMark PRO main breaker plug-on neutral load centers arrive with a main circuit breaker installed for a convenient and swift install. Main circuit breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The PM3212C features spaces for 32 - 1" circuit breakers and 64 circuits, a 125-ampere bus rating, copper bus bars, and a gray combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RI
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	32
1" Space	32
1/2" Space	0
Amperage	125 A
Circuit Breaker Style	Plug-On Neutral
Device type	Main Breaker
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Combination
Factory Installed Ground Kit	Bonding screw included
Feed	Either
Input/Output Voltage	120/240V ac
Interrupt Rating	22k
Interrupting Capacity Rating	22
Load Center Type	Plug-On Neutral Load Centers
NEMA Rating	NEMA 1
No of Circuits	64
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----



Dimensions

Depth	3.805 in
Width	14.11 in