



Representative Image

Catalog No. PM815RFL

Description: LOAD CTR MCB 150A 8CKT N3R GRAY PON FTL

UPC No 783164641028

Home > Load Centers > Load Centers

PowerMark PRO main breaker plug-on neutral load centers arrive with a main circuit breaker installed for a convenient and swift install. Main circuit breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The PM815RFL features spaces for 8 - 1" circuit breakers and 16 circuits, a 150-ampere bus rating, copper bus bars, factory installed feed-through lugs, and a NEMA 3R enclosure.

Descriptors

Category	Load Centers
GO Schedule	RI
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	8
1" Space	8
1/2" Space	0
Amperage	150 A
Circuit Breaker Style	Plug-On Neutral
Device type	Main Breaker
Door	Yes
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface
Factory Installed Ground Kit	Bonding screw included
Feed	Top
Input/Output Voltage	120/240V ac
Interrupt Rating	22k
Interrupting Capacity Rating	22
Load Center Type	Plug-On Neutral Load Centers
NEMA Rating	NEMA 3R
No of Circuits	16
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----


by ABB

Dimensions

Depth	3.805 in
Width	14.11 in