



Representative Image

Catalog No. RB250

Description: INS NYL FEM-250 DISC 16-14 LEN 0.91

UPC No 786210818160

Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect

Nylon Insulated Female Disconnect, Length .91 Inches, Width .29 Inches, Maximum Insulation .162, Tab Size .250x.032, Wire Range #16-#14, Color Blue, Copper, Tin Plated, 1,000 Pack

Descriptors

Category	Wire terminal disconnect
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

Specifications

Material	Brass
Finish	Tin Plated
Color	Blue
Insulation	Nylon/Polyamide

Classifications

Brand Name	Sta-Kon
Standard	UL E66716 UL E66716

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially isolated
Colour insulation	Blue
Material insulation	PA
Material	Copper
AWG-range	16-14