



Representative Image

Catalog No. RB2573

Description: FULLY INS NYL FEM-250 DISC, 16

UPC No 786210856803

Home > Connectivity & Grounding > Sta-Kon > Wire terminal disconnect

Nylon Fully Insulated Female Disconnect, Length 1.01 Inches, Width .38 Inches, Maximum Insulation .185, Tab Size .250x.032, Wire Range #16-#14 AWG, Color Blue, Brass, Tin Plated, 1,000 Pack

Descriptors

Category	Wire terminal disconnect
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.

Specifications

Material	Brass
Finish	Tin Plated
Color	Blue
Insulation	Nylon/Polyamide

Classifications

Brand Name	Sta-Kon
Standard	UL E66716

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Fully isolated
Colour insulation	Blue
Material insulation	PA
Material	Brass
AWG-range	16-14

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622701	N/A	N/A	N/A
CSA	7222	622701	N/A	N/A	N/A
UL	E66716	N/A	N/A	N/A	N/A