



Representative Image

## Catalog No. RBC717M

**Description:** VNYL INS HVDTY RNG TERM 16-14 TAPE

**UPC No** 786210187938

**Home > Connectivity & Grounding > Sta-Kon > Electrical terminals**

Vinyl Insulated Heavy-Duty Ring Terminal, Length 1.19 Inches, Width .51 Inches, Maximum Insulation .210, Bolt Hole 1/4 Inch, Wire Range #16-#14 Heavy Duty AWG, Color Blue, Copper, Tin Plated, On Mylar Tape, 500 Pack

### Descriptors

|          |                      |
|----------|----------------------|
| Category | Electrical terminals |
|----------|----------------------|

### Specifications

|          |       |
|----------|-------|
| Material | Vinyl |
| Color    | Blue  |

### Classifications

|            |         |
|------------|---------|
| Brand Name | Sta-Kon |
|------------|---------|

### Dimensions

|           |           |
|-----------|-----------|
| Wire Size | 16-14 AWG |
|-----------|-----------|

|                      |                                                            |
|----------------------|------------------------------------------------------------|
| ETIM                 | EC001052 Solderless copper terminals for copper conductors |
| Flange shape         | Ring shape                                                 |
| Insulation           | Polyvinyl chloride (PVC)                                   |
| Colour insulation    | Blue                                                       |
| Reel packaging       | Y                                                          |
| AWG-range            | 16-14                                                      |
| Material             | Copper                                                     |
| Surface protection   | Tinned                                                     |
| Stud size (imperial) | 1/4 inch                                                   |