



Catalog No. RBC873YM

Description: INS NYL RING TRM 14-12 HVDTY No10

UPC No 67396016657

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Nylon Insulated Heavy-Duty Ring Terminal, Length 1.04 Inches, Width .39 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #16-#14 Heavy Duty, Color Yellow, Copper, Tin Plated, On Mylar Tape, 500 Pack

Descriptors

Category	Electrical terminals
----------	----------------------

Specifications

Voltage Rating	300 V
Material	Nylon
Color	Yellow

Classifications

Brand Name	Sta-Kon
------------	---------

Dimensions

Wire Size	14-12 AWG
-----------	-----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Yellow
Reel packaging	Y
AWG-range	16-14
Material	Copper
Surface protection	Tinned
Stud size (imperial)	10

by ABB