



Catalog No. RC363ML

Description: NYL RING, 12-10, No10, LEFT REEL

UPC No 67396016916

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Nylon Insulated Ring Terminal, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #10, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, On Left Feed Reel Mylar Tape, 500 Pack

Descriptors

Category	Electrical terminals
----------	----------------------

Specifications

Material	Nylon
Color	Yellow

Classifications

Brand Name	Sta-Kon
------------	---------

Dimensions

Wire Size	12-10 AWG
-----------	-----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Yellow
Reel packaging	Y
AWG-range	12-10
Material	Copper
Surface protection	Tinned
Stud size (imperial)	10