



Catalog No. RC863UFR

Description: NYLON RING 10-12 No8 BOLT 45DEG REV

UPC No 786209995605

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Nylon Insulated Ring Terminal with 45 Degree Reverse Bend, Length 1.00 Inches, Width .37 Inches, Maximum Insulation .210, Bolt Hole #8, Wire Range #12-#10 AWG, Color Yellow, Copper, Tin Plated, 500 Pack

Descriptors

Category	Electrical terminals
----------	----------------------

Specifications

Material	Nylon
Color	Yellow

Classifications

Brand Name	Sta-Kon
------------	---------

Dimensions

Wire Size	12-10 AWG
-----------	-----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 233 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Yellow
Reel packaging	N
AWG-range	12-10
Material	Copper
Surface protection	Tinned
Stud size (imperial)	8

by ABB