



Representative Image

Catalog No. SH724LMV

Description: B24 SIDE ENT SGL LOCK SYS 1XPG29-1

UPC No 786209987143

Home > Connectivity & Grounding > Pos-E-Kon > Terminal block covers

Side entry single post hood, NPT entry-1 Inch x 1 Inch

Descriptors

Category	Terminal block covers
----------	-----------------------

Specifications

Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Temperature Rating	-40 to +257 F

Classifications

Brand Name	Pos-E-Kon
Standard	UL E215386

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant

ETIM	EC000437 Housing for rectangular connectors
Width	43.0022 mm
Height	64.9986 mm
Type of housing	Other
Material housing	Aluminium
Coating housing	Powder coating
Position cable feed	Sideways
With cable screw gland	N
With hinged lid	N
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125 °C
Degree of protection (IP), mounted	Other

by ABB