



Representative Image

## Catalog No. TH224MV

**Description: TOP ENTRY DBL POST HOOD 1X3/4IN B24**

**UPC No 786209987174**

**Home > Connectivity & Grounding > Pos-E-Kon > Terminal block covers**

Top entry double post hood, NPT entry-1 Inch x 3/4 Inch

### Descriptors

Category	Terminal block covers
----------	-----------------------

### Specifications

Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Temperature Rating	-40 to +257 F

### Classifications

Brand Name	Pos-E-Kon
Standard	UL E215386

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000437 Housing for rectangular connectors
Width	43.0022 mm
Height	64.9986 mm
Type of housing	Other
Material housing	Aluminium
Coating housing	Powder coating
Position cable feed	Above
With cable screw gland	N
With hinged lid	N
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125 °C
Degree of protection (IP), mounted	Other

by ABB