



Representative Image

Catalog No. TH316HMV

Description: B16 DBL LOCK SYS 1XPG29

UPC No 786209987402

Home > Connectivity & Grounding > Pos-E-Kon > Terminal block covers

Top entry double post hood, NPT entry-1 Inch x 1 Inch

Descriptors

Category	Terminal block covers
----------	-----------------------

Specifications

Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Voltage Rating	600 VAC
Temperature Rating	-40 to +257 F

Classifications

Brand Name	Pos-E-Kon
Standard	UL e215386, CSA 70013

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000437 Housing for rectangular connectors
Width	43.0022 mm
Height	75.9968 mm
Type of housing	Other
Material housing	Aluminium
Coating housing	Powder coating
Position cable feed	Above
With cable screw gland	N
With hinged lid	N
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125 °C



ETIM	EC000437 Housing for rectangular connectors
Degree of protection (IP), mounted	Other