

Catalog No. TH816MV

Description: B16 TOP ENT SGL LOCK SYS 1XPG21-3/4

UPC No 786209987242

Home > Connectivity & Grounding > Pos-E-Kon > Terminal block covers

Top entry single post hood, NPT entry-1 Inch x 3/4 Inch

Representative Image

Descriptors

Category	Terminal block covers
----------	-----------------------

Specifications

Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Voltage Rating	600 VAC
Temperature Rating	-40 to +257 F

Classifications

Brand Name	Pos-E-Kon
Standard	UL e215386, CSA 70013

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC000437 Housing for rectangular connectors
Width	43.0022 mm
Height	64.9986 mm
Type of housing	Other
Material housing	Aluminium
Coating housing	Powder coating
Position cable feed	Above
With cable screw gland	N
With hinged lid	N
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125 °C
Degree of protection (IP), mounted	Other

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	70013	623301	N/A	N/A	N/A
UL	E215386	N/A	ECBT2	N/A	N/A