



Representative Image

Catalog No. THQB32030

Description: THQB MCB 30A 10KA 3P 240V

UPC No 783164012415

Home > Circuit Breakers > Miniature Circuit Breakers > Q-Line Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QB breakers are bolt-on versions of the Q Line used for bolting to the bus connections of load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications. 2030 Amps 30 A

Descriptors

Category	Q-Line Miniature Circuit Breakers
Product Line	TEY / Q-Line (Bolt-On)
GO Schedule	EB

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	30 A
System Voltage	120 Vac 120/240 Vac 240 Vac
Poles	3
Trip Function	LI
Continuous Current Rated	Standard
120 Vac Interrupting Rating	10 KAIC
120/240 Vac Interrupting Rating	10 KAIC
240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Long Time	Fixed
Instantaneous	Fixed
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

Classifications

UL File #	E11592
-----------	--------

by ABB