



Representative Image

## Catalog No. TM24415C

**Description: 150A 24CRT 3P4W 208Y/120V 10KIC CMB**

**UPC No 783164189988**

**Home > Load Centers > Load Centers**

Main breaker load centers arrive with a main breaker installed for a convenient and swift install. Main breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The TM24415CB features spaces for 24, 1" breakers, a 150A main ampere rating, 3 phases, a bottom feed, and a combination/flush enclosure.

### Descriptors

Category	Load Centers
GO Schedule	R7

### Specifications

# Branch Circuit 250A	24
1" Space	24
1/2" Space	0
Amperage	150 A
Circuit Breaker Style	Plug-In
Device type	Main Breaker
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Combination
Factory Installed Ground Kit	No
Feed	Top
Input/Output Voltage	208Y/120V ac
Interrupting Capacity Rating	22
Load Center Type	Standard
NEMA Rating	NEMA 1
Phase	3 Phase
Service & Voltage	3 Phase, 4 Wire, 208Y/120V ac
Wires	4 Wire

### Classifications

UL/CUL Listing	UL
----------------	----

### Dimensions

Depth	3.7 in
Height	33.2 in
Weight	34.0 lb

**by ABB**

## Dimensions

Width

14.0 in