

Catalog No. TY28M-10

Description: CABLE TIE 400X4.8MM 220N WHITE BULK

UPC No 786210122021

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, White Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum or as a Flexible Cable and Conduit Support, Length of 361mm (14.2 Inches), Width of 4.67mm (0.184 Inch), Thickness of 1.09mm (0.043 Inch), Maximum Bundle Diameter 102mm (4 Inches), Tensile Strength Rating of 220 Newtons (50 Pounds), Bulk Pack

Representative Image

Descriptors

Category | Cable ties

Specifications

Material	Nylon/Polyamide 6.6
Color	White
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 220 newtons

Classifications

Brand Name | Ty-Rap

Dimensions

Width	0.184 in , 4.67 mm
Length	14.2 in , 361 mm
Thickness	0.043 in , 1.09 mm
Bundle Diameter	4 in , 101.6 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant

ETIM	EC000046 Cable tie
Band width	0.19 inch
Band width	4.8 mm
Length belt/tape/tie	361 mm
Length belt/tape/tie	14.2 inch
Tie thickness	1.3 mm

by ABB

ETIM	EC000046 Cable tie
Tie thickness	0.05 inch
Max. bundle diameter	102 mm
Max. bundle diameter	4.02 inch
Min. holding force	220 N
Operation temperature	-60-+105 °C
Operation temperature	-76-+221 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Halogen free	Y
Colour	White
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y