

Catalog No. TY525M-8

Description: CABLE TIE 50LB 7 INCH GR NYLON 2-PC

UPC No 786209889720

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Gray Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185.67mm (7.31 Inches), Width of 4.67mm (0.184 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Military Specified (MIL-SPEC MS3367-1-8)

Representative Image

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Gray
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 220 newtons

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Width	0.184 in , 4.67 mm
Length	7.31 in , 185.67 mm
Thickness	0.043 in , 1.09 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant