



Representative Image

Catalog No. WE-TY23M-1

Description: CBL TIE 18LB 4IN BROWN NYLON 2-PC

UPC No 786210735702

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Brown Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 91.95mm (3.62 Inches), Width of 2.29mm (0.09 Inches), Thickness of 0.75mm (0.03 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Special Pack

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Brown
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Width	0.09 in , 2.29 mm
Length	3.62 in , 91.95 mm
Thickness	0.03 in , 0.75 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC000046 Cable tie
Band width	2.29 mm
Length belt/tape/tie	91.95 mm
Length belt/tape/tie	3.62 inch
Tie thickness	0.75 mm
Tie thickness	0.03 inch
Min. holding force	80 N
Model	Internal toothing

by ABB

ETIM	EC000046 Cable tie
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Brown
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y