

Catalog No. WE-TY23M-2

Description: CBL TIE 18LB 4 RED NYLON 2-PC BU

UPC No 786210066011

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Red Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 91.95mm (3.62 Inches), Width of 2.29mm (0.09 Inches), Thickness of 0.75mm (0.03 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Special Pack

Representative Image

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Red
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Width	0.09 in , 2.29 mm
Length	3.62 in , 91.95 mm
Thickness	0.03 in , 0.75 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	2.29 mm
Length belt/tape/tie	91.95 mm
Tie thickness	0.75 mm
Tie thickness	0.03 inch
Min. holding force	80 N

ETIM	EC000046 Cable tie
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Red
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y