

Catalog No. WE-TY25M-1

Description: CABLE TIE 50LB 7 IN BROWN NYLON 2PC

UPC No 786210918723

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Brown Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185.67mm (7.31 Inches), Width of 4.67mm (0.184 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Special Pack

Representative Image

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Brown
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 220 newtons

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Width	0.184 in , 4.67 mm
Length	7.31 in , 185.67 mm
Thickness	0.043 in , 1.09 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	4.67 mm
Length belt/tape/tie	185.67 mm
Length belt/tape/tie	7.31 inch
Tie thickness	1.09 mm
Tie thickness	0.043 inch

by ABB

ETIM	EC000046 Cable tie
Min. holding force	222 N
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Brown
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y