

Catalog No. WE-TY27M-8-C

Description: CABLE TIE 120LB 13 GRAY NYLON 2-PC

UPC No 786210652504

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Gray Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 457.20mm (18.00 Inches), Width of 6.86mm (0.27 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 540 Newtons (120 Pounds), Special Packs x50

Representative Image

Descriptors

Category	Cable ties
----------	------------

Specifications

Material	Nylon/Polyamide 6.6
Color	Gray
Lock Mechanism	Stainless Steel Barb
Tensile Strength	120 pounds , 540 newtons

Classifications

Brand Name	Ty-Rap
------------	--------

Dimensions

Width	0.27 in , 7 mm
Length	13.4 in , 340 mm
Thickness	0.06 in , 1.65 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Length belt/tape/tie	330.2 mm
Length belt/tape/tie	13 inch
Min. holding force	530 N
Model	Internal toothing
Band closure	Steel nose

ETIM	EC000046 Cable tie
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Grey
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N