

**Alternate Catalog No. SU202M-K50**  
**Catalog No. 2CDS272337R0577**

**Description:** UL489 MCB 2P K 50A 240

**UPC No** 4016779932813

**Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs**

SU202M-K50 Miniature Circuit Breaker K-Char., 10kA, 50A, 2P UL489



Representative Image

**Descriptors**

|          |                            |
|----------|----------------------------|
| Category | UL 489 Branch Circuit MCBs |
|----------|----------------------------|

**Specifications**

|                                                |                                                     |
|------------------------------------------------|-----------------------------------------------------|
| Number of Poles                                | 2                                                   |
| Tripping Characteristic                        | K                                                   |
| Rated Current                                  | 50 A                                                |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489          |
| Product Main Type                              | SU200M                                              |
| Rated Voltage (V)                              | (240 V AC)<br>(96 V DC)                             |
| Interrupting Rating acc. to UL489              | (240 V AC) 10 kA<br>(96 V DC) 10 kA                 |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                    |
| Power Loss                                     | 9 W<br>at Rated Operating Conditions per Pole 4,5 W |