



Representative Image

Catalog No. 9T21B9103G03

Description: "1A,15kVA,240x480-120/240,115C,3R,ES,QMS"

UPC No 783173030479

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	15.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	Y
Sub Type	Buck Boost Autotransformer
Frequency	60 Hz
Impedance	0.00 %
FrameSize	19500
Net Weight	220
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	220
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions	
Width	12.5 in
Depth	12.5 in
Height	17.1 in