



Representative Image

Alternate Catalog No. SU202MR-K63
Catalog No. 2CDS272347R0607

Description: MCB SU200MR RTT 2P K 63A BCP

UPC No 4016779957656

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU202MR-K63 MCB K-Char., 10kA, 63A, 2P, RTT UL 489, Ring Cable Lug

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	2
Tripping Characteristic	K
Rated Current	63 A
Product Main Type	SU200MR
Rated Voltage (V)	(240 V AC) (96 V DC)
Interrupting Rating acc. to UL489	(240 V AC) 10 kA (96 V DC) 10 kA
Power Loss	at Rated Operating Conditions per Pole 5.4 W