



Representative Image

Alternate Catalog No. PSTX85-600-70
Catalog No. 1SFA898108R7000

Description: "PSTX85, 600V, 100-250VAC"

UPC No 7320500501306

Home > Soft Starters > Softstarter - Open (PSTX)

Descriptors

Category	Softstarter - Open (PSTX)
----------	---------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	80
Normal Duty: Motor Power (HP) at 208V	25
Normal Duty: Motor Power (HP) at 230V	30
Normal Duty: Motor Power (HP) at 460V	60
Normal Duty: Motor Power (HP) at 575V	75
Heavy Duty: Output Current (A)	68
Heavy Duty: Motor Power (HP) at 208V	20
Heavy Duty: Motor Power (HP) at 230V	25
Heavy Duty: Motor Power (HP) at 460V	50
Heavy Duty: Motor Power (HP) at 575V	60
Power Dissipation In Watts	6.5
Height (Inches)	12.4
Width (Inches)	5.9
Depth (Inches)	7.7

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Weight (lb)	13.4
Height (mm)	314
Width (mm)	150
Depth (mm)	197.5

Dimensions

Weight (kg)

6.1