



Representative Image

Catalog No. 9T51B0003

Description: "1C,0.075kVA,240x480-120/240,55C,3R,60,QB"

UPC No 783173008256

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T5

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	0.075 KVA
Coil Material	CU
TempRise	55.0 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	6200
Net Weight	6
TempClass	105.0 °C
AmbTemp	40.0 °C
InsulSys	CLASSA
EnergyEfficiency	None
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	6
Sound	Std
GSA Compliance	Yes

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions

Width	5.1 in
Depth	3.2 in
Height	6.4 in